



Snipe nose pliers, straight VDE insulated, overall length: 160mm



Order data

| | |
|--------------|---------------|
| Order number | 713300 160 |
| GTIN | 4003773033806 |
| Item class | 73F |

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws chrome-plated, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

| | |
|---------------------|---------------------------------------------------|
| overall length | 160 mm |
| Jaw length | 50 mm |
| Handle | Multi-component covering |
| Jaw design | snipe-nosed, straight |
| Standard | DIN EN IEC 60900 / VDE 0682-201 |
| Standard | DIN ISO 5745 |
| Jaw characteristics | Cutting edges induction hardened (approx. 60 HRC) |
| Type of jaws | inner face roughened |
| Material | Chromium vanadium steel |

| | |
|-----------------|-----------------------|
| Surface | chrome-plated |
| Type of product | Multi-function pliers |