

**Needle nose pliers angled 45°, overall length: 160mm****Order data**

Order number	715100 160
GTIN	4003773046790
Item class	73F

Description**Version:**

With particularly long and slim snipe nose jaws. Tapering to 3 mm wide and 1 mm high at the tip. Smooth jaws. Jaws chemically blacked, polished head, plastic coated handles.

With 45° angled jaws.

Standard:

DIN ISO 5743

Material:

Chrome vanadium electro-steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Jaw length	55 mm
Jaw design	snipe-nosed pliers, angled 45°
Standard	DIN ISO 5743
Type of jaws	inner face smooth
Handle	plastic coated
Material of pliers	Chrome vanadium electro-steel, drop-forged and oil-hardened
Surface of pliers	chemically blackened, head bright polished

Type of product

Pipe grip pliers