



Snipe nose pliers, angled chrome-plated, with grips, overall length: 160mm



Order data

Order number	713500 160
GTIN	4003773016007
Item class	73F

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Pliers chrome-plated, handles with multi-component covering. Twist-tolerant flexible precision tips.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Jaw length	50 mm
Jaw design	snipe-nosed, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	Multi-component covering

Material	Chrome vanadium steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Multi-function pliers