

**Snipe nose pliers, straight, polished, overall length: 125mm****Order data**

Order number	713150 125
GTIN	4003773015932
Item class	73F

Description**Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chemically blackened, head bright polished. Plastic coated handles. Twist-tolerant flexible precision tips.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	125 mm
Jaw length	27 mm
Handle	plastic coated
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Material	Chromium vanadium steel

Surface	chemically blackened, head bright polished
Type of product	Multi-function pliers