

Garant**Snipe nose pliers, straight VDE insulated, overall length: 160mm****Order data**

Order number	713310 160
GTIN	4045197501462
Item class	71B

Description**Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Jaw length	50 mm
Handle	Multi-component covering with non-slip Haptoprene surface
Jaw design	snipe-nosed, straight
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)

Type of jaws	inner face roughened
Material	Chromium vanadium steel
Surface	chrome-plated
Type of product	Multi-function pliers