



## Snipe nose pliers, angled dip insulated to VDE, overall length: 200 mm



### Order data

Order number	713735 200
GTIN	4003773016090
Item class	73F

### Description

#### Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws. **Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V**

Jaws chrome-plated, plastic coated handles, **dip insulated.**

#### Standard:

**DIN ISO 5745**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Jaw length: 73 mm

### Technical description

overall length	200 mm
Jaw length	73 mm
Jaw design	snipe-nosed with angled jaws (approx. 40° - 45°)
Standard	DIN EN 60900 / VDE 0682-201
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened

Handle	plastic coated
Material	Chrome vanadium steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Multi-function pliers