

**Snipe nose pliers, angled, polished, overall length: 160mm****Order data**

Order number	713550 160
GTIN	4003773015994
Item class	73F

Description**Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chemically blackened, head bright polished. Plastic coated handles. Twist-tolerant flexible precision tips.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Jaw length	50 mm
Jaw design	snipe-nosed, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	plastic coated
Material	Chrome vanadium steel, drop-forged and oil-hardened

Surface	chemically blacked
Type of product	Multi-function pliers