



Snipe nose pliers, straight dip insulated to VDE, overall length: 200mm



Order data

Order number	713335 200
GTIN	4003773016069
Item class	73F

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Jaws chrome-plated, plastic coated handles, **dip insulated**.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	200 mm
Jaw length	73 mm
Handle	dip insulated
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Standard	DIN EN IEC 60900 / VDE 0682-201
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened

Material	Chromium vanadium steel
Surface	chrome-plated
Type of product	Multi-function pliers