



Snipe nose pliers, angled, polished, overall length: 200mm



Order data

Order number	713550 200
GTIN	4003773022848
Item class	73F

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chemically blackened, head bright polished. Plastic coated handles. Twist-tolerant flexible precision tips.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	200 mm
Jaw length	73 mm
Jaw design	snipe-nosed, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	plastic coated
Material	Chrome vanadium steel, drop-forged and oil-hardened

Surface	chemically blacked
Type of product	Multi-function pliers