

Assembly tool set, 59 pieces without container



Order data

Order number	680305
GTIN	2050001017697
Item class	66H

Description

Application:

Contains high quality tools for **maintenance and repair of systems, machines, equipment etc.**

Supplied with:

STABILA® wooden folding rule: 1 pc. No. 466005 size 2

Wire brush: 1 pc. No. 575000 size 3

DICK workshop files set, 2nd cut with handle, assorted, in a tool roll: 1 pc. No. 517200 size 200 (5-piece)

PUK® universal hacksaw: 1 pc. No. 581220 size 150

GARANT open-ended spanners set 6 – 34 mm with clip: 1 pc. No. 610610 size 12 (6×7 – 30×34 mm) with 1 pc. No. 611500 size 12

Hexagon key L-wrench set with a plastic clip: 1 pc. No. 626072 size 8 (2 - 10 mm)

PB Swiss Tools slot-head screwdriver set: 1 pc. No. 660910 size 5 (3.5 - 8 mm)

PB Swiss Tools offset screwdriver for slot-head: 1 pc. No. 664800 size 6.5

PB Swiss Tools voltage tester up to 250 V: 1 pc. No. 665020 size 3.5

PB Swiss Tools screwdriver for Phillips: 1 pc. each No. 668100 size 1; 2

KNIPEX® combination pliers: 1 pc. No. 701500 size 180

KNIPEX® water pump pliers: 1 pc. No. 705500 size 250

KNIPEX® pincers: 1 pc. No. 706610 size 210

Universal grip wrench: 1 pc. No. 708205 size 250

KNIPEX® snipe nose pliers with side cutter: 1 pc. No. 713150 size 160

Internal circlip pliers, straight: 1 pc. No. 719805 size J2

External circlip pliers, straight: 1 pc. No. 719905 size A2

KNIPEX® side cutter: 1 pc. No. 724900 size 160

RENNSTEIG cold chisel: 1 pc. No. 740500 size 175

RENNSTEIG taper pin punch set and centre punch: 1 pc. No. 745600 size 6 (2 - 6 mm; 120 mm)

Engineer's hammer with hickory handle: 1 pc. No. 750110 size 300

Plastic hammer: 1 pc. No. 754500 size 32

PB Swiss Tools reamer: 1 pc. No. 831700 size 110

Fixed blade cable knife: 1 pc. No. 844300 size 175

Plastic bottle oiler: 1 pc. No. 083532 size 125

Insulating tape, black: 1 pc. No. 083654 size BLACK

Marker pen, blue: 1 pc. No. 085154 size B

Note:

Tool is supplied loose.

Technical description

Type of product	Tool set
-----------------	----------

Accessories

Snipe nose pliers, straight, polished overall length 160 mm	713150 160
Plastic oiler with discharge tube Capacity 125 ml	083532 125
Square reamer with plastic handle Blade length 110 mm	831700 110
Screwdriver for Phillips, with "multicraft" power grip Cross-head size 2	668100 2
Fixed blade cable knife	844300
Heavy-duty pincers overall length 210 mm	706610 210
Grooved water pump pliers, chemically blacked overall length 250 mm	704900 250
Screwdriver for Phillips, with "multicraft" power grip Cross-head size 1	668100 1
Engineer's hammer with handle protection collar Weight without handle 300 g	750110 300
Insulating tape Colour BLACK	083654 BLACK
Circlip pliers Type A2	719905 A2
Combination pliers, polished overall length 180 mm	701500 180

Voltage tester special quality Blade width 3,5 mm	665020 3,5
Universal grip wrench, jaw shape Vee Overall length 250 mm	708205 250
Circlip pliers Type J2	719805 J2
Screwdriver set for slot-head, with "multicraft" power grip Number of screwdrivers 5	660910 5
Hexagon key L-wrench setnickel-plated Number of screwdrivers 8	626072 8
Offset screwdriver for slot-head Blade width b 6,5 mm	664800 6,5
Set of engineer's files, 5 pieces, in a tool rollCut 2 Length without tang 200 mm	517200 200
Plastic hammer with Cellidor inserts Hammer head Ø 32 mm	754500 32
Wire hand brushSmooth steel wire 0.35 mm Number of rows of bristles 3	575000 3
Flat chisel overall length 175 mm	740500 175
Double open ended spanner set Number of keys 12	610610 12
Taper pin punch setin a plastic holder Number of tools 6	745600 6
Dura-Ink® 15 permanent marker Writing colour B	085154 B
Diagonal side cutter polished overall length 160 mm	724900 160
General-purpose hacksaw "PUK" with general-purpose blade (310)Fixed handle	581220
Plastic clip holder for number of sockets 12	611500 12
Wooden folding rule, yellow Length 2 m	466005 2