

## Assembly tool set, 107 pieces without container



### Order data

Order number	680355
GTIN	2050001016799
Item class	66H

### Description

#### Application:

Contains high quality tools for **maintenance and repair of systems, machines, equipment etc.**

#### Supplied with:

Dividers: 1 pc. No. 457600 size 200

Scriber, double-ended: 1 pc. No. 458400

**STABILA**® wooden folding rule: 1 pc. No. 466005 size 2

**DICK** workshop files set, 2nd cut with handle, assorted, in a tool roll: 1 pc. No. 517200 size 200 (5-piece)

Precision key files in a plastic wallet: 1 pc. No. 518930 (6-piece)

Wire brush, 3-row: 1 pc. No. 575000 size 3

Hacksaw frame with blade: 1 pc. No. 580700 size 300

**GARANT** mini bow saw: 1 pc. No. 581195

**GARANT** open-ended spanner 6 – 34 mm with clip: 1 pc. No. 610610 size 12 (6×7 – 30×34 mm) with 1 pc. No. 611500 size 12

**GARANT** double-ended ring spanner, 6 – 22 mm: 1 pc. No. 615610 size 8 (6×7 - 19×22 mm)

Hexagon key L-wrench set in a plastic clip: 1 pc. No. 626072 size 9 (1.5 - 10 mm)

Torx® key L-wrench: 1 pc. No. 624857 size 8 (TX6 – TX25)

Socket set 1/2 inch: 1 pc. No. 637718 size 6 (16 pieces)

**GARANT** slot-head screwdriver set: 1 pc. No. 660036 size 5 (3.5 - 8 mm)

**PB Swiss Tools** slot-head screwdriver, short: 1 pc. No. 664100 size 6.5

**PB Swiss Tools** offset screwdriver for slot-head: 1 pc. No. 664800 size 6.5

**PB Swiss Tools** voltage tester up to 250 V: 1 pc. No. 665020 size 3.5

**GARANT** screwdriver for Phillips: 1 pc. each No. 667702 size 1; 2

Combination pliers: 1 pc. No. 703000 size 180  
 Water pump pliers: 1 pc. No. 706151 size 250  
**KNIPEX**® pincers: 1 pc. No. 706610 size 210  
 Universal grip wrench: 1 pc. No. 708205 size 250  
 Snipe nose pliers with side cutter: 1 pc. No. 713200 size 160  
 Internal circlip pliers, straight: 1 pc. No. 719805 size J2  
 External circlip pliers, straight: 1 pc. No. 719905 size A2  
 Diagonal side cutter: 1 pc. No. 725250 size 160  
**RENNSTEIG** cold chisel: 1 pc. No. 740500 size 175  
**RENNSTEIG** cold cross-cut chisel: 1 pc. No. 740600 size 150  
**RENNSTEIG** taper pin punch set and centre punch: 1 pc. No. 745600 size 6 (2 - 6 mm; 120 mm)  
 Engineer's hammer with 3-component handle: 1 pc. each No. 750450 size 300; 500  
 Plastic hammer: 1 pc. No. 754500 size 32  
 Ideal sheet metal shears with compound action: 1 pc. No. 766042 size 260  
 Electrician's scissors: 1 pc. No. 769005 size 130  
**PB Swiss Tools** reamer: 1 pc. No. 831700 size 110  
 Fixed blade cable knife: 1 pc. No. 844300 size 175  
 Plastic bottle oiler: 1 pc. No. 083532 size 125  
 Torch, LED light: 1 pc. No. 081437 size BLACK  
 Insulating tape, black: 1 pc. No. 083654 size BLACK  
 Marker pen, blue: 1 pc. No. 085154 size B

**Note:****Tool is supplied loose.**


---

**Technical description**

Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081557 LR3
Power supply	Battery-powered
Type of product	Tool set

---

**Accessories**

Wire hand brush Smooth steel wire 0.35 mm Number of rows of bristles 3	575000 3
Fixed blade cable knife	844300
Dividers Length L 200 mm	457600 200

Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 1	667690 1
Mini bow saw Ergonomic handle	581195
Offset screwdriver for slot-head Blade width b 6,5 mm	664800 6,5
Engineer's hammer with 3-component handle Weight without handle 500 g	750450 500
Precision key files set, 6 pieces in plastic case	518930
Circlip pliers Type A2	719905 A2
Heavy-duty pincers overall length 210 mm	706610 210
Water pump pliers with plastic coating Overall length 250 mm	706151 250
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667690 2
Dura-Ink® 15 permanent marker Writing colour B	085154 B
Circlip pliers Type J2	719805 J2
Socket set 1/2 inch square drive 16 pieces Type 6	637718 6
Hexagon key L-wrench set nickel-plated Number of screwdrivers 9	626072 9
Double open ended spanner set Number of keys 12	610610 12
Plastic oiler with discharge tube Capacity 125 ml	083532 125
Hacksaw frame 317 with bimetal blade 24 tpi	580700
Flat chisel overall length 175 mm	740500 175
Taper pin punch set in a plastic holder Number of tools 6	745600 6
Voltage tester special quality Blade width 3,5 mm	665020 3,5
Plastic hammer with Cellidor inserts Hammer head Ø 32 mm	754500 32
Set of engineer's files, 5 pieces, in a tool roll Cut 2 Length without tang 200 mm	517200 200
Cross-cut chisel overall length 150 mm	740600 150
Torx® key L-wrench set phosphated Number of screwdrivers 11	624870 11
	769005 130

Electrician's scissors nickel-plated with wire-cutter overall length 130 mm	
Engineer's hammer with 3-component handle Weight without handle 300 g	750450 300
Snipe nose pliers, straight, bright finished overall length 160 mm	713200 160
Universal grip wrench, jaw shape Vee Overall length 250 mm	708205 250
LED torch with batteries Colour BLACK	081437 BLACK
Insulating tape Colour BLACK	083654 BLACK
Screwdriver for slot-head, short Blade width b 6,5 mm	664100 6,5
Vanadium combination pliers, bright finished overall length 180 mm	703000 180
Screwdriver set for slot-head, with 2-component Haptoprene handle Number of screwdrivers 5	660031 5
Square reamer with plastic handle Blade length 110 mm	831700 110
Angle scribe	458400
Diagonal side cutter, bright finish overall length 160 mm	725250 160
Ideal snips with 2-component handles overall length 260 mm	766042 260
Double-ended ring spanner set, deeply cranked Number of keys 8	615500 8
Plastic clip holder for number of sockets 12	611500 12
Wooden folding rule, yellow Length 2 m	466005 2