

Assembly tool set, 90 pieces with GARANT tool case



Order data

Order number	680275
GTIN	2050001016867
Item class	66H

Description

Application:

Contains a **basic set of very high quality tools** for **maintenance and repair of equipment, machines, appliances etc.**

Supplied with:

WIHA plastic folding rule 2 m: 1 pc. No. 466200 size 2

DICK high-performance flat file with handle: 1 pc. No. 515000 size 200

GARANT mini bow saw: 1 pc. No. 581195

GARANT combination spanner set: 1 pc. No. 613610 size 9 (5.5 - 19 mm)

PB Swiss Tools L-wrench set for Torx®: 1 pc. No. 624810 size 8 (TX6 - TX25)

GARANT hexagon key L-wrench set with ball point and retention function, in a plastic clip: 1 pc. No. 627132 size 9 (1.5 - 10 mm)

GARANT socket set 1/4 inch: 1 pc. No. 630299 size 6 (39 pieces)

GARANT slot-head screwdriver set: 1 pc. No. 660036 size 6 (3.5 - 10 mm)

GARANT screwdriver for Phillips: 1 pc. each No. 667702 size 1; 2

GARANT combination pliers: 1 pc. No. 700940 size 180

KNIPEX® water pump pliers: 1 pc. No. 705800 size 250

GARANT snipe nose pliers, angled: 1 pc. No. 713440 size 200

KNIPEX® internal circlip pliers, straight: 1 pc. No. 719790 size J2

KNIPEX® external Circlip pliers, straight: 1 pc. No. 719890 size A2

GARANT side cutters: 1 pc. No. 724840 size 160

PB Swiss Tools chisel taper pin punch set: 1 pc. No. 745100 (6-piece)

Engineer's hammer with 3-component handle: 1 pc. No. 750450 size 300

Combined engineer's hammer and soft hammer: 1 pc. No. 754880 size 30

GARANT tool case: 1 pc. No. 692790

Note:

Tool is supplied loose.

Technical description

Type of product	Tool set
-----------------	----------

Accessories

Multi-purpose hand file with handle, special cut Length without tang 200 mm	515000 200
Precision circlip pliers Type A2	719890 A2
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 1	667690 1
Engineer's hammer with 3-component handle Weight without handle 300 g	750450 300
Screwdriver set for slot-head, with 2-component Haptoprene handle Number of screwdrivers 6	660031 6
Plastic folding rule Length 2 m	466200 2
Socket set 1/4 inch square drive 39 pieces Type 6	630299 6
Hexagon key L-wrench set, with retainer ball chrome-plated Number of screwdrivers 9	627132 9
Snipe nose pliers, angled, chrome-plated, with grips overall length 200 mm	713440 200
Water pump pliers Cobra® chemically blacked overall length 250 mm	705800 250
Combination hammer Hammer head Ø 30 mm	754880 30
Combination spanner set Number of keys 9	613610 9
Service tool case of X-ABS with shaft pockets	692790
Precision circlip pliers Type J2	719790 J2

Combination pliers, chrome-plated, with 2-component grips overall length 180 mm	700940 180
Chisel and taper pin punch set in a plastic holderspecial quality Number of tools 6	745100 6
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667690 2
Combination spanner set Number of keys 9	613510 9
Torx® key L-wrench setchrome-plated Number of screwdrivers 8	624810 8
Mini bow sawErgonomic handle	581195
Diagonal side cutter chrome-plated, with grips overall length 160 mm	724840 160
Assembly tool set, 90 pieceswithout tool case	680280