

Tool set V / 100 pieces – basic set



Order data

Order number	680570
GTIN	2050001021854
Item class	66H

Description

Application:

Popular assortments for keeping in roller cabinets, workbenches, drawer cabinets etc.

Supplied with:

Tajima pocket tape measure: 1 pc. No. 462300 size 5

DICK half-round file 200 mm, cut: 1 pc. No. 513200 size 200

Hardwood file handle: 1 pc. No. 519400 size 120

Precision key file set in metal case: 1 pc. No. 518950 (6-piece)

Steel wire hand brush: 1 pc. No. 575000 size 4

GARANT open-ended spanner set: 1 pc. No. 610610 size 10 (6×7 - 27×30 mm)

GARANT double-ended ring spanner set: 1 pc. No. 615610 size 10 (6×7 - 27×30 mm)

Hexagon key L-wrench set: 1 pc. No. 626072 size 8 (2 - 10 mm)

Socket set, 1/2 inch, including drive accessories: 1 pc. No. 638018 size 12 (33-piece)

Slot-head screwdriver set: 1 pc. No. 660711 size 5 (3.5 - 8 mm)

Voltage tester 150 – 250 V: 1 pc. No. 665014 size 2.5

PB Swiss Tools slot-head screwdriver short: 1 pc. No. 664100 size 6.5

PB Swiss Tools screwdriver for Phillips, short: 1 pc. No. 668000 size 2K

Screwdriver set for Phillips: 1 pc. No. 668411 size 3 (1-3)

GARANT heavy duty combination pliers chrome-plated: 1 pc. No. 700340 size 180

KNIPEX® water pump pliers: 1 pc. No. 705700 size 250

GARANT side cutters chrome-plated: 1 pc. No. 724840 size 160

RENNSTEIG cold chisel: 1 pc. No. 740500 size 175

RENNSTEIG taper pin punch set and centre punch: 1 pc. No. 745600 size 6 (2 - 6 mm; 120mm)

Engineer's hammer: 1 pc. No. 750125 size 500

Wera plastic mallet with polyurethane inserts: 1 pc. No. 754200 size 32

PB Swiss Tools bradawl 200 mm long with plastic handle: 1 pc. No. 831600 size 110

RENNSTEIG three-edge hollow scraper with wooden handle: 1 pc. No. 836010 size 150

RENNSTEIG flat scraper with wooden handle: 1 pc. No. 837020 size 200

Tajima universal knife, 18 mm blade: 1 pc. No. 845030 size 2K

Plastic oiler with brass tube: 1 pc. No. 083529 size 80

Telescopic magnetic retriever: 1 pc. No. 081650 (length 160 – 670 mm)

Torch, LED light: 1 pc. No. 081437 BLACK

Technical description

Article no of the battery / rechargeable battery fitted	081557 LR3
Number of batteries contained	3
Type of product	Tool set

Accessories

Flat chisel overall length 175 mm	740500 175
Flat scraper Blade length 200 mm	837020 200
Triangular hollow-ground scraper Blade length 150 mm	836010 150
Double open ended spanner set Number of keys 10	610610 10
Piercing awl with plastic handle Blade length 110 mm	831600 110
Half round file Length without tang 200 mm	513200 200
Screwdriver set for slot-head, with power grip Number of screwdrivers 5	660711 5
Diagonal side cutter chrome-plated, with grips overall length 160 mm	724840 160
Socket set 1/2 inch square drive 33 pieces Type 12	638018 12
Screwdriver for slot-head, short Blade width b 6,5 mm	664100 6,5
Plastic hammer with polyurethane inserts Hammer head Ø 32 mm	754200 32

Hexagon key L-wrench setnickel-plated Number of screwdrivers 8	626072 8
Engineer's hammer Weight without handle 500 g	750125 500
Screwdriver for Phillips, with plastic handle Cross-head size 2K	668000 2K
Voltage tester special quality Blade width 2,5 mm	665020 2,5
LED torchwith batteries Colour BLACK	081437 BLACK
Tape measureextra sturdy Band length 5 m	462300 5
Heavy-duty combination pliers, chrome-plated, with two-component grips overall length 180 mm	700340 180
Screwdriver set for Phillips, with power grip Number of screwdrivers 3	668411 3
Hardwood file handle Overall length 100 mm	519400 100
Precision key files set, 6 piecesin metal case	518950
Telescopic magnetic retriever	081650
Wire hand brushSmooth steel wire 0.35 mm Number of rows of bristles 4	575000 4
General-purpose knife with 2-component handlewith 1 blade, 18 mm	845030
Small plastic bottle oiler Capacity 80 ml	083529 80
Taper pin punch setin a plastic holder Number of tools 6	745600 6
Grooved water pump pliers, chrome-plated overall length 250 mm	705000 250
Double-ended ring spanner set, deeply cranked Number of keys 10	615500 10