



## Precision circlip pliers, Type: A1



### Order data

Order number	719890 A1
GTIN	4003773048725
Item class	73F

### Description

#### Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring. Form A – straight jaws.**

#### Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

#### Application:

For fitting and removing circlips.

#### Standard:

**DIN 5254 A und B** – für Außensicherungsringe.

### Technical description

overall length	140 mm
Tip Ø	1.3 mm
Shape	A
for external circlips Ø	10 - 25 mm
Standard	DIN 5254 A

Use of circlip pliers	Outer ring, straight
Jaw shape	straight
Handle	plastic coated
Material	Special steel
Surface	chemically greyed
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers