



Precision circlip pliers, Type: J41



Order data

Order number	719790 J41
GTIN	4003773048664
Item class	73F

Description

Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles.

With inserted precision tips. Form D –90° angled jaws.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing Circlips.

Standard:

DIN 5256 C und D – für Innensicherungsringe.

Technical description

for internal circlips Ø	85 - 140 mm
Shape	D
Tip Ø	3.2 mm
overall length	305 mm
Standard	DIN 5256 D
Use of circlip pliers	Inner ring, angled
Jaw shape	90° angled

Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	chemically greyed
with over-expansion guard	no
Handle with self-grip mechanism	yes
Exchangeable points	no
Type of product	Circlip Pliers