



## Precision circlip pliers, Type: A2



### Order data

|              |               |
|--------------|---------------|
| Order number | 719890 A2     |
| GTIN         | 4003773048732 |
| Item class   | 73F           |

### Description

#### Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring. Form A – straight jaws.**

#### Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

#### Application:

For fitting and removing circlips.

#### Standard:

**DIN 5254 A und B** – für Außensicherungsringe.

### Technical description

|                         |            |
|-------------------------|------------|
| Tip Ø                   | 1.8 mm     |
| Shape                   | A          |
| for external circlips Ø | 19 - 60 mm |
| overall length          | 180 mm     |
| Standard                | DIN 5254 A |

|                                    |                      |
|------------------------------------|----------------------|
| Use of circlip pliers              | Outer ring, straight |
| Jaw shape                          | straight             |
| Handle                             | plastic coated       |
| Material                           | Special steel        |
| Surface                            | chemically greyed    |
| with over-expansion guard          | no                   |
| Joint with integral opening spring | yes                  |
| Handle with self-grip mechanism    | no                   |
| Exchangeable points                | no                   |
| Type of product                    | Circlip Pliers       |