



Precision circlip pliers, Type: A3



Order data

Order number	719890 A3
GTIN	4003773048749
Item class	73F

Description

Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring**. **Form A – straight jaws**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Use of circlip pliers: Outer ring, straight

overall length: 225 mm

for external circlips \varnothing : 40 - 100 mm

Tip \varnothing : 2.3 mm

Technical description

overall length	225 mm
for external circlips \varnothing	40 - 100 mm
Shape	A

Tip Ø	2.3 mm
Standard	DIN 5254 A
Use of circlip pliers	Outer ring, straight
Jaw shape	straight
Handle	plastic coated
Material	Special steel
Surface	chemically greyed
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers