



Precision circlip pliers with over-expansion guard, Type: J1



Order data

Order number	719792 J1
GTIN	4003773073864
Item class	73F

Description

Version:

With adjustable limit stop.

Form C – straight jaws.

Form D – 90° angled jaws.

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles.

With inserted precision tips.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing Circlips.

Standard:

DIN 5256 C und D – für Innensicherungsringe.

Technical description

Tip Ø	1.25 mm
overall length	140 mm
for internal circlips Ø	12 - 25 mm
Shape	C
Standard	DIN 5256 C

Use of circlip pliers	Inner ring, straight
Jaw shape	straight
Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	chemically greyed
with over-expansion guard	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers