

**Cordless pop rivet nut setting tool FireBird®****Order data**

Order number	770520
GTIN	4007081260039
Item class	74A

Description**Version:**

Cordless tool for blind rivet nuts up to M10 aluminium, up to M8 steel and up to M6 stainless steel. Attention: Please order a free adapter plug No. 08 1172_GB.

Advantage:

Very powerful, large number of rivet nuts per battery charge. Easy and reliable twisting on of blind rivet nuts. Electronic control of the setting stroke used. Quick-change system for threaded spigots.

Supplied with:

1 each threaded spigot and nozzle M4, M5 and M6, 1 hexagon L-wrench, 2x double open-ended spanners size 24x27, Li-ion battery No. 770527, and battery charger No. 770528 size 1 in a plastic case.

Technical description

Setting force	13000 N
Weight including rechargeable battery	2.1 kg
Battery capacity	2 Ah

Battery voltage	14.4 V
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Pop riveter

Accessories

Spare nozzle with threaded spigot Type M4	770522 M4
Spare nozzle with threaded spigot Type M5	770522 M5
Spare nozzle with threaded spigot Type M6	770522 M6
Li-ion quick-change battery Capacitance 2,0 A·h	770527 2,0
Battery charger Type 1	770528 1