



Circlip pliers, Type: A6



Order data

| | |
|--------------|---------------|
| Order number | 719895 A6 |
| GTIN | 4003773025009 |
| Item class | 73F |

Description

Version:

Handles of steel plate with locking mechanism. **Form A – straight jaws.**

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Technical description

| | |
|-----------------------------------|----------------------|
| for external circlips \emptyset | 252 - 400 mm |
| Shape | A |
| overall length | 570 mm |
| Tip \emptyset | 4.5 mm |
| Standard | DIN 5254 A |
| Use of circlip pliers | Outer ring, straight |
| Jaw shape | straight |
| Handle | plastic coated |

| | |
|---------------------------------|----------------------------------|
| Material | Rolled steel, high-tensile |
| Material of point | Special tool steel, oil-hardened |
| Surface | black powder-coated |
| Handle with self-grip mechanism | yes |
| Exchangeable points | yes |
| Type of product | Circlip Pliers |

Accessories

| | |
|--|-----------|
| Pair of tips for circlip pliers Shape A6 | 719910 A6 |
|--|-----------|