

**Garant****Precision circlip pliers, Type: J2****Order data**

Order number	719770 J2
GTIN	4045197504012
Item class	71B

**Description****Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles.

**With inserted precision tips. Form C – straight jaws.**

**Advantage:**

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

**Application:**

For fitting and removing Circlips.

**Standard:**

**DIN 5256 C und D** – für Innensicherungsringe.

**Technical description**

for internal circlips Ø	19 - 60 mm
Shape	C
Tip Ø	1.8 mm
overall length	180 mm
Standard	DIN 5256 C
Use of circlip pliers	Inner ring, straight
Jaw shape	straight

Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers