



## Precision circlip pliers, Type: J2



### Order data

Order number	719790 J2
GTIN	4003773048534
Item class	73F

### Description

#### Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles.

**With inserted precision tips. Form C – straight jaws.**

#### Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

#### Application:

For fitting and removing Circlips.

#### Standard:

**DIN 5256 C und D** – für Innensicherungsringe.

### Technical description

overall length	180 mm
Shape	C
for internal circlips $\varnothing$	19 - 60 mm
Tip $\varnothing$	1.8 mm
Standard	DIN 5256 C
Use of circlip pliers	Inner ring, straight
Jaw shape	straight

Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	chemically greyed
with over-expansion guard	no
Handle with self-grip mechanism	yes
Exchangeable points	no
Type of product	Circlip Pliers