

Garant**Precision circlip pliers, Type: A01****Order data**

Order number	719870 A01
GTIN	4045197504142
Item class	71B

Description**Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles. Joint with **integral opening spring**. **Form B –90° angled jaws**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Technical description

Tip Ø	0.9 mm
for external circlips Ø	3 - 10 mm
overall length	130 mm
Shape	B
Standard	DIN 5254 B

Use of circlip pliers	Outer ring, angled
Jaw shape	90° angled
Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers