



## Circlip pliers, Type: J6



### Order data

Order number	719795 J6
GTIN	4003773024927
Item class	73F

### Description

#### Version:

Handles of steel plate with locking mechanism.

**With inserted precision tips. Form C – straight jaws.**

#### Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

#### Application:

For fitting and removing Circlips.

#### Standard:

**DIN 5256 C und D** – für Innensicherungsringe.

### Technical description

Shape	C
overall length	580 mm
for internal circlips $\varnothing$	252 - 400 mm
Tip $\varnothing$	4.5 mm
Standard	DIN 5256 C
Use of circlip pliers	Inner ring, straight
Jaw shape	straight
Material	Rolled steel

Material of point	Special tool steel, oil-hardened
Surface	black powder-coated
Handle with self-grip mechanism	yes
Exchangeable points	yes
Type of product	Circlip Pliers

---

## Accessories

Pair of tips for circlip pliers Shape J6	719810 J6
------------------------------------------	-----------