



Precision circlip pliers, Type: A31



Order data

Order number	719890 A31
GTIN	4003773048848
Item class	73F

Description

Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring. Form B –90° angled jaws.**

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Technical description

for external circlips \emptyset	40 - 100 mm
overall length	210 mm
Tip \emptyset	2.3 mm
Shape	B
Standard	DIN 5254 B
Use of circlip pliers	Outer ring, angled
Jaw shape	90° angled

Handle	plastic coated
Material	Special steel
Surface	chemically greyed
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers