



## Precision circlip pliers, Type: A41



### Order data

Order number	719890 A41
GTIN	4003773048855
Item class	73F

### Description

#### Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring. Form B –90° angled jaws.**

#### Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

#### Application:

For fitting and removing circlips.

#### Standard:

**DIN 5254 A und B** – für Außensicherungsringe.

### Technical description

overall length	305 mm
Shape	B
Tip Ø	3.2 mm
for external circlips Ø	85 - 140 mm
Standard	DIN 5254 B
Use of circlip pliers	Outer ring, angled

Jaw shape	90° angled
Handle	plastic coated
Material	Special steel
Surface	chemically greyed
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers