



## Precision circlip pliers, Type: J01



### Order data

Order number	719790 J01
GTIN	4003773048619
Item class	73F

### Description

#### Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles.

**With inserted precision tips. Form D –90° angled jaws.**

#### Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

#### Application:

For fitting and removing Circlips.

#### Standard:

**DIN 5256 C und D** – für Innensicherungsringe.

Use of circlip pliers: Inner ring, angled

overall length: 130 mm

for internal circlips  $\varnothing$ : 8 - 13 mm

Tip  $\varnothing$ : 0.9 mm

### Technical description

for internal circlips $\varnothing$	8 - 13 mm
Shape	D
overall length	130 mm
Tip $\varnothing$	0.9 mm
Standard	DIN 5256 D

Use of circlip pliers	Inner ring, angled
Jaw shape	90° angled
Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	chemically greyed
with over-expansion guard	no
Handle with self-grip mechanism	yes
Exchangeable points	no
Type of product	Circlip Pliers