

Garant**Precision circlip pliers, Type: J11****Order data**

Order number	719770 J11
GTIN	4045197504050
Item class	71B

Description**Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles.

With inserted precision tips. Form D –90° angled jaws.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing Circlips.

Standard:

DIN 5256 C und D – für Innensicherungsringe.

Technical description

Shape	D
overall length	130 mm
for internal circlips Ø	12 - 25 mm
Tip Ø	1.25 mm
Standard	DIN 5256 D
Use of circlip pliers	Inner ring, angled
Jaw shape	90° angled

Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers