

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/09mm

Order data

Order number	250037 16/09
GTIN	4045197925923
Item class	21T

Description
Version:

PCLNL 95° boring bars for indexable inserts CN..

Technical description

suitable indexable insert	CN.. 09T3..
Lever	259015 11
ISO code toolholder	A16M PCLNR/L09
Overall length L	150 mm
Setting angle κ	95 degrees
Clamping height L_2	15.25 mm
Centre offset L_3	11 mm
Lever screw	259018 9
Insert size	9 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500