

**Pair of gloves 6230, Glove size: 10****Order data**

Order number	094236 10
GTIN	4059904093805
Item class	09H

Description**Version:**

6230. Anti-static gloves for **ESD** applications. Also for use of **touch screens**.

Standard:

EN 388; EN ISO 21420

EN 16350

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

Technical description

Touch sensitivity	very good
silicone-free	no
Oil grip	medium
EN 388 cut resistance	1

Accuracy of fit	good
EN 388 penetration resistance	1
Breathability	good
EN 388 abrasion resistance	4
Material of coating	PU
Glove size	10
Heat protection	not available
Wet grip	medium
EN 388 tear propagation resistance	3
DMF-free	no
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Suitable for touch screens
Knitted technology	13G
electrostatic characteristic	EGB/ESD
Application	reusable
EN 388	3141X
Backing material	Nylon/carbon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	white / grey
Weight	14 g
Type of product	ESD gloves