

**Pair of gloves Camapur® Comfort 616+, Glove size: 10****Order data**

Order number	094245 10
GTIN	4008198761600
Item class	04Q

**Description****Version:**

Camapur® Comfort 616+. Due to their thin coating the gloves afford the user particularly good touch sensitivity. Despite which they have a relatively good mechanical abrasion resistance. Washable, thereby increasing their working life.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Manufacturer's designation	Camapur Comfort 616+
Accuracy of fit	very good
DMF-free	yes
Breathability	very good
Glove size	10

Touch sensitivity	very good
Wet grip	medium
silicone-free	no
Material of coating	PU
Oil grip	medium
Heat protection	not available
Series	Camapur®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	10
electrostatic characteristic	0.6 sec. in accordance with charge decay specifications in EN 61340-5-1
EN 388	3131X
Backing material	Polyamide
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	240 - 260 mm
Colour	white
Weight	36 g
Knitted technology	13G
Application	reusable
Cut protection class	1
Type of product	Multi-purpose gloves