

Ansell**Pair of gloves HyFlex® 11-618, Glove size: 11****Order data**

Order number	094260 11
GTIN	10076490488786
Item class	04P

Description**Version:**

HyFlex® 11-618. Lightweight glove with a very good combination of cut protection, oil repellence and increased durability. Extremely thin and yet robust gloves of **18-gauge** knitted fabric. Particularly suitable for light assembly work with high demands on precision, final assembly of electric motors, air conditioning systems, wiring harnesses.

Version of the advertising text:

Thin fine knitted gloves for light assembly work where high precision is required.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	11
silicone-free	no
DMF-free	no

Breathability	very good
Heat protection	not available
Wet grip	medium
Accuracy of fit	very good
Touch sensitivity	very good
Oil grip	good
Material of coating	PU
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12
Glove characteristics	Suitable for allergy sufferers
EN 388	3121X
Backing material	Nylon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	195 mm
Colour	black / blue
Weight	7,4 g
Knitted technology	18G
Application	reusable
Material	PU
Cut protection class	FG
Type of product	Multi-purpose gloves