

**Pair of gloves 6230, Glove size: 11****Order data**

Order number	094236 11
GTIN	4059904125773
Item class	09H

**Description****Version:**

**6230.** Anti-static gloves for **ESD** applications. Also for use of **touch screens**.

**Standard:**

EN 388; EN ISO 21420

EN 16350

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

**Technical description**

Accuracy of fit	good
Breathability	good
Glove size	11
Material of coating	PU

silicone-free	no
EN 388 cut resistance	1
EN 388 penetration resistance	1
EN 388 tear propagation resistance	3
Heat protection	not available
Oil grip	medium
Wet grip	medium
Touch sensitivity	very good
DMF-free	no
EN 388 abrasion resistance	4
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Suitable for touch screens
Knitted technology	13G
electrostatic characteristic	EGB/ESD
Application	reusable
EN 388	3141X
Backing material	Nylon/carbon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	white / grey
Weight	14 g
Type of product	ESD gloves