

Groove width gauge with numerical tolerance, Type: F



Order data

Order number	484410 F
GTIN	2050001956682
Item class	48B

Description

IMPORTANT: item is configurable

Nominal size: 21.001 - 25.999 mm, Intervall: 0,001

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Z; ZA; ZB; ZC; ZC

Quality: 10; 11; 12; 13; 7; 8; 9

Version:

Groove width gauges with "Go" and "No Go" end. "Go" end with **wear allowance** to DIN 7164.

Gauge body of hardened steel.

For intermediate sizes or numerical tolerances.

Application:

For checking flat fits, e.g. grooves.

Standard:

Toleranzen und Abmaße nach **DIN 1938-1, DIN 2245-1 und DIN 7163.**

Note:

The size designation type describes the nominal dimension in millimetres (mm).

Type A = 3.001 – 5.999

Type B = 6.001 – 8.999

Type C = 9.001 – 12.999

Type D = 13.001 – 16.999

Type E = 17.001 – 20.999

Type F = 21.001 – 25.999

Example: 15.8 m6 or 41.04 + 0.01 / – 0.02.

Calibration: L6

Nominal size: 21.001 - 25.999 mm

Technical description

Nominal size	21.001 - 25.999 mm
Tolerance zone	G
Tolerance zone	A
Tolerance zone	B
Tolerance zone	C
Tolerance zone	CD
Tolerance zone	D
Tolerance zone	E
Tolerance zone	EF
Tolerance zone	F
Tolerance zone	FG
Tolerance zone	J
Tolerance zone	H
Tolerance zone	JS
Tolerance zone	K
Tolerance zone	M
Tolerance zone	P
Tolerance zone	N
Tolerance zone	R
Tolerance zone	S
Tolerance zone	U
Tolerance zone	T
Tolerance zone	V
Tolerance zone	X
Tolerance zone	Z
Tolerance zone	ZC
Tolerance zone	ZA
Tolerance zone	ZB
Tolerance zone	ZC

Standard	DIN 2245-1
Standard	DIN 7163
Standard	DIN 1938-1
Quality	7
Quality	8
Quality	9
Quality	10
Quality	11
Quality	12
Quality	13
Calibration	L6
Type of product	Shaft slot gauge

Services

Calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	018400 60
DAkkS calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	019620 60
Labelling laser-etched Type	018940
DAkkS calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	028340 60
Calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	028300 60