

Garant
Tool24 Smartline – cabinet system, Type: S11M-EN

Order data

Order number	979099 S11M-EN
GTIN	4045197926142
Item class	9SA

Description
Version:

Flexible goods issuing system for storage and management of machining and assembly tools, measuring tools, protective work-wear and many other consumable items. Master systems can be extended using the optional extension cabinets (slave system). The individual software packages allow the systems to be tailored to your exact requirements.

Body and doors made of 1 mm sheet metal. Pallet truck base made of 1.75 mm sheet metal. Storage shelf made of bamboo

Application:

Automatic goods issuing system for storage and management of tools and accessories.

Content:

Dividers: 10 pcs. No. 960310 size 4+18; 1 pc. No. 960330 size 3+14

Fitted with:

Number of drawers × drawer front height: 1 technical drawer
10×75 mm; 1×150 mm

Supplied with:

Master system: Tool issuing cabinet with 11 drawers 36×36 units, touch screen, barcode scanner, PC including ATMS.NG software package and dividing material.

Supplied with:

Touch screen 22 inch, barcode scanner, PC including ATMS.NG software package

Colour:

Body light grey RAL 7035, drawers signal blue RAL 5005 **powder-coated**.
 Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
 Drawer/pull-out shelf load capacity: 75 kg
 Storage area: 4 m²
 Height: 1390 mm
 Width: 717 mm
 Depth: 750 mm
 Drawer usable width: 612 mm
 Drawer usable depth: 612 mm

Technical description

Width	717 mm
Type	Basic master cabinet, complete
Drawer/pull-out shelf load capacity	75 kg
Storage area	4 m ²
Depth	750 mm
Number of drawers	11
Drawer usable width	612 mm
Drawer usable depth	612 mm
Division within a drawer	36×36 units
Height	1390 mm
Weight	249 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system