



Workshop vernier caliper with mm and inch graduations, Measuring range: 1000mm



Order data

Order number	415100 1000
GTIN	4045197927699
Item class	41Z

Description

Version:

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

Technical description

Internal jaw \varnothing	20 mm
Calibration	A1
Packaging	sturdy box
Graduation	1/128 in
Jaw length	150 mm
Graduation	1/20 mm
Standard	ISO 13385
Measurement deviation E MPE	± 0.15 mm
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX

Type of product

Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm

021000 1000

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm

021010 1000