



Workshop vernier caliper with mm and inch graduations, Measuring range: 200mm



Order data

| | |
|--------------|---------------|
| Order number | 415100 200 |
| GTIN | 4045197927668 |
| Item class | 41Z |

Description

Version:

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

Technical description

| | |
|-----------------------------|-----------------------|
| Jaw length | 60 mm |
| Packaging | sturdy box |
| Calibration | A1 |
| Internal jaw \varnothing | 10 mm |
| Graduation | 1/20 mm |
| Graduation | 1/128 in |
| Standard | ISO 13385 |
| Measurement deviation E MPE | ± 0.05 mm |
| Vernier graduations mm/inch | yes |
| Measurement technology | analogue |
| Material | Stainless steel, INOX |

Type of product

Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm

021000 200

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm

021010 200