

**Digital depth gauge, Measuring range: 50mm****Order data**

Order number	418760 50
GTIN	4045197927682
Item class	42A

Description**Version:**

Digital depth gauge with **absolute scale**, no zeroing required. Very high accuracy due to the glass scale. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Calibration	A1
Reversible reading	0.01 mm
Reversible reading	0.0005 in
Needle hole probe length	6 mm
Needle hole probe Ø	1.5 mm
Error limit	0.02 mm
Bridge length	50 mm
Number of batteries contained	1
Power supply	Battery-powered
Standard	Works standard

Reversible reading	mm / inch
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236