

Ansell**Pair of gloves HyFlex® 11-600, Glove size: 8****Order data**

Order number	094240 8
GTIN	10076490499331
Item class	04P

Description**Version:**

HyFlex® 11-600. Fine knitted gloves with palm coating for dry working conditions. For precision work, highly breathable. With a thin layer of backing material for use in industry and light and fine work for which **maximum freedom of movement** is required. Protects the product against fingerprints, residues from the gloves themselves and general dirt. Particularly suitable for the assembly of small components such as ball bearings, joints and springs.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Heat protection	not available
Touch sensitivity	very good
Accuracy of fit	very good
Glove size	8

Oil grip	medium
DMF-free	no
silicone-free	no
Breathability	very good
Wet grip	medium
Material of coating	PU
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12
EN 388	3121A
Backing material	Nylon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	200 mm
Colour	white
Weight	11,6 g
Knitted technology	15G
Application	reusable
Material	PU
Cut protection class	A
Type of product	Multi-purpose gloves