



Pipe bender (bending segment and bending lever), for pipe outer Ø: 8 mm



Order data

Order number	823000 8
GTIN	4004625245088
Item class	86B

Description

Version:

The device consists of only 2 components (bending former and bending lever), which are easily screwed together. A slide shoe facilitates bending and prevents pipe deformation.

Application:

For cold bending of **hard** and soft copper pipe, soft steel pipe, thin-walled stainless steel pipe, plain or clad. Bending angles up to 180°. Up to 1 mm wall thickness.

Bending radius (centre of pipe): 22 mm

Technical description

for pipe outer Ø	8 mm
Bending radius (centre of pipe)	22 mm
maximum bending angle	180 °
Type of product	Bending machine