

Garant
CNMG 190624, Grade: HB7140-1


Order data

Order number	250176 HB7140-1
GTIN	4045197927965
Item class	21G

Description

CNMG 190624 HB7140-1 Grade: HB7140-1
 Chip breaker: VM
 Tolerance: M
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 60 - 230 m/min

Technical description

Chip breaker	VM
Cutting depth a_p	0.5 - 4 mm
Feed f	0.1 - 0.4 mm/rev.
Corner radius	2.4 mm
Grade	HB7140-1
Cutting speed v_c main application	60 - 230 m/min
Cutting conditions	slightly interrupted

Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CNMG 190624
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning