

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 16/09mm

Order data

Order number	260724 16/09
GTIN	4045197927781
Item class	21T

Technical description

Overall length L	150 mm
ISO code toolholder	A16M SSKCR/L09
Pack of insert screws	269028 8
Insert size	9 mm
Setting angle κ	75 degrees
Minimum pre-drill $\varnothing D_{\min}$	20 mm
suitable indexable insert	SC.. 09T3..
Overhang L_1	48 mm
Clamping height L_2	15.25 mm
Centre offset L_3	11 mm
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500