

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 16/09mm

Order data

| | |
|--------------|---------------|
| Order number | 260725 16/09 |
| GTIN | 4045197927798 |
| Item class | 21T |

Technical description

| | |
|--|-------------------------------|
| Centre offset L_3 | 11 mm |
| Insert size | 9 mm |
| Pack of insert screws | 269028 8 |
| Clamping height L_2 | 15.25 mm |
| Setting angle κ | 75 degrees |
| Minimum pre-drill $\varnothing D_{\min}$ | 20 mm |
| Overhang L_1 | 48 mm |
| suitable indexable insert | SC.. 09T3.. |
| ISO code toolholder | A16M SSKCR/L09 |
| Overall length L | 150 mm |
| Shank $\varnothing D_s$ | 16 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500