



## Pneumatic impact wrench, Type: W2911



### Order data

Order number	079171 W2911
GTIN	7322590051303
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.  
Powerful impact wrench.

Exhaust air passes through the handle, **reversible**.

- **Powerful impact hammer mechanism.**
- **Low weight combined with high performance.**
- **Composite body and handle with long working life.**
- **Three torque settings.**
- **Ergonomic handle with good insulation.**
- **Reversal changeover by two buttons.**

#### Application:

Suitable for heavy-duty use.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

Maximum screw Ø (8.8 - 12.9)	M14
maximum speed	7300 min <sup>-1</sup>
Manufacturer's designation	W2911
Reversible	yes
Torque range	150 - 400 Nm
Format	Pistol
Height	178 mm
Weight	1.2 kg
Operating noise	92 dB(A)
Tool arbor drive profile	□
Length	160 mm
recommended hose size (internal Ø)	10 mm
maximum vibration to EN	5.1 m/s <sup>2</sup>
Tool arbor size	1/2 in
maximum air consumption	1020 l/min
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver