

**Garant**
**Clamping toolholder, left-hand, Shank / insert size: 32/16mm**

**Order data**

Order number	251707 32/16
GTIN	4045197928252
Item class	21T

**Technical description**

Insert size	16 mm
Head length L <sub>1</sub>	32 mm
Shank size	32 mm
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	VN.. 1604..
Clamping claw	259038 2
Overall length L	170 mm
Shim	259031 39
ISO code toolholder	MVJNR/L 3225P16
Shim screw	259025 3
Screw for clamping claw	259021 1
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500