

Garant
Clamping toolholder, neutral, Shank / insert size: 32/16mm

Order data

Order number	251712 32/16
GTIN	4045197928269
Item class	21T

Technical description

Shim	259031 39
suitable indexable insert	VN.. 1604..
Functional width L ₄ neutral holders	12.5 mm
Shim screw	259025 3
Shank size	32 mm
Screw for clamping claw	259021 1
ISO code toolholder	MVVNN 3225P16
Overhang L ₁ neutral holders	45 mm
Insert size	16 mm
Clamping claw	259038 2
Overall length L neutral holders	170 mm
Series	QuickTurn
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500