


Garant**Jaw with positioning pins, for jaw width: 160mm****Order data**

| | |
|--------------|---------------|
| Order number | 362627 160 |
| GTIN | 4045197928290 |
| Item class | 31S |

Description**Version:**

- **Hardened steel, Tenifer gas nitrided (tolerance ± 0.01 mm).**
- **Simple to fit on the vice.**
- **Pins pushed in mechanically.**
- **Compressed air operation via valves on both sides.**
- **The fixed and movable jaws are identical.**
- **Requires a 5.5 bar compressed air supply**

Application:

Quick changeover for different machining operations.

- **Quick and fully repeatable positioning accuracy.**
- **Eliminates tedious fitting of jaw inserts.**

Suitable for:

GARANT NC No. 360510; 360465; 361290.

HOLEX No. 362010.

Allmatic No. 360405; 360600; 360605; 361180; 361202; 361302; 361304; 362250; 362350 and with clamping jaws No. 361400 – 361620.

Supplied with:

1 fastening screw.

Technical description

| | |
|--------------------------|-------------------|
| suitable for colour code | TC |
| suitable for colour code | Titan2/TitanSense |
| suitable for colour code | HD-Allmatic |
| suitable for colour code | HD-HOLEX |
| suitable for colour code | HiPo |
| suitable for colour code | LC |
| suitable for colour code | NC8 |
| Type of product | Vice jaws |

Accessories

| | |
|-------------------------------|----------|
| Spare pins, pack of 10 Type 1 | 362629 1 |
|-------------------------------|----------|