

**Digital external micrometer with measuring tip, Measuring range: 0-25mm****Order data**

Order number	421726 0-25
GTIN	4045197928917
Item class	42B

Description**Version:**

Easy to read digital display with additional analogue reading. Robust metal casing.
Rotating measurement spindle, carbide-tipped measuring faces

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357

Micrometer barrel graduations: 1/50

IP Index of Protection: IP 54

Calibration: B1

Scale divisions: 0.001 mm

Scale divisions: 0.00005 in

Error limit: 4 µm

Technical description

Scale divisions	0.001 mm
Scale divisions	0.00005 in
Calibration	B1
Number of batteries contained	1
Error limit	4 µm
Article no of the battery / rechargeable battery fitted	081560 357

IP Index of Protection	IP 54
Power supply	Battery-powered
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Reversible reading	mm / inch
Micrometer barrel graduations	1/50
Type of product	External micrometer

Services

Calibration External tube micrometer maximum measuring range 25 mm	012050 25
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100
Labelling laser-etched Type	018940
Calibration External tube micrometer maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer maximum measuring range 100 mm	022010 100

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------