

Garant**Mini-boring bar, carbide, right-hand, Overhang L1 / insert size d: 29/8mm****Order data**

| | |
|--------------|---------------|
| Order number | 270006 29/8 |
| GTIN | 4045197928979 |
| Item class | 21V |

Description**Version:**

Low-vibration carbide shank with soldered steel head and hardened insert seat.

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to perform.**

Technical description

| | |
|--------------------------------|------------|
| Overall length L | 95 mm |
| Insert size | 08 mm |
| Clamping height L ₂ | 11.5 mm |
| Insert screw | 279815 11 |
| Head length L ₁ | 29 mm |
| Shank Ø D _s | 12 mm |
| Application type | right-hand |
| Through-coolant | yes |
| Type of product | Boring bar |

Accessories

Data sheet

| | |
|--|-------------|
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10 | 674248 TX10 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |