

**Garant****Mini-boring bar, carbide, right-hand, Overhang L1 / insert size d: 56/8mm****Order data**

Order number	270006 56/8
GTIN	4045197928986
Item class	21V

**Description****Version:**

Low-vibration carbide shank with soldered steel head and hardened insert seat.

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to perform.**

**Technical description**

Head length L <sub>1</sub>	56 mm
Overall length L	120 mm
Insert screw	279815 11
Insert size	08 mm
Clamping height L <sub>2</sub>	11.5 mm
Shank Ø D <sub>s</sub>	12 mm
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10

674248 TX10

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500